

Proxidyne Annunciator

Proxidyne Annunciator plays a recorded message to customers in the aisle when triggered by customer activity detected by in-aisle sensors. Use Annunciator for loss prevention and flow control.

Simply install the Proxidyne Annunciator anywhere that you want to play a recorded message. When triggered wirelessly, the Annunciator will play a specified message at an adjustable volume. View analytics or change announcements in Proxidyne Dashboard.



Features

- Alerts customers in aisles and fitting rooms by playing a recorded announcement
- Installs quickly with mounting bracket (included), screws, zip-ties or adhesive tape
- Control announcements automatically and wirelessly
- Trigger an announcement with a Motion Sensor, Button or other sensor
- Easily update sounds using MP3 format and SD Card slot
- Change announcements by inserting an SD Card
- Create announcements in standard MP3 file formats
- Includes sample software (Python) for easy integration with your project

Requirements

- SD Card of at least 1GB
- A Proxidyne Sensor: Button or Motion
- You may use up to 100 Proxidyne Sensors — any combination of buttons and other sensors — with one Proxidyne Annunciator.

A staff member
will be right
with you.



Learn more today!
Contact us at 1-630-305-9604
sales@proxidyne.com
www.proxidyne.com



© 2016-2017 Proxidyne, Inc. • V. 4.1

Technical Specifications

Audio	MP3 file files upgradeable via SD card slot
Proxidyne Sensors	Trigger audio announcements remotely
Sensor Limit	Use with up to 100 Proxidyne Sensors
Network Connectivity	Wireless Bluetooth 4.1
Power	USB 5V power from battery or AC adapter
Range	Standard Range up to 150 ft, extendable to over 1 km using the Proxidyne Long Range Relay
Security	AES-128 Encryption
Connector	USB Type-A Mini connector for configuration and power
Upgrades	Upgradeable firmware via USB



The Proxidyne Annunciator requires one Proxidyne Button or Motion Sensor. One Annunciator can be used with up to 100 Buttons and Motion Sensors.

